

Features

- Intended for use with all Insight AC-powered deck- and wall-mount touchless faucets. One supply powers one Insight faucet.
- Single supply power cord plugs into any global electrical outlet except North America. For North America outlets please use 13480-A.
- Input for 120-240 V, 50/60-Hertz operation.
- Regulated output of 5 VDC at 1.2 Amps.
- Energy Efficiency Level VI.
- Short circuit and overcurrent protection with auto reset.
- Interchangeable plug blades for Europe, UK and Australia.
- CE compliant.
- Meets German Product Safety Act (GS).




Codes/Standards

None Applicable

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required.

120/240 V, 0.3 A, 50/60 Hz

Notes

Install this product according to the installation guide.

Technical Information

All product dimensions are nominal.