



**Undertone®**  
Under-mount Kitchen Sink  
**K-3184**

**Features**

- 21-inch minimum base cabinet width.
- 18-gauge stainless steel.
- Under-mount.
- Single compartment.
- 7-5/8" (194 mm) deep bowl.
- SilentShield® sound-absorption technology offers quieter performance.
- 18-1/2" (470 mm) x 15-3/4" (400 mm)

**Recommended Accessories**

- K-6377 Sponge Caddy
- K-6378 Kitchen Brush Caddy
- K-6379 Kitchen Squeegee

**Optional Accessories**

- K-8801 Sink Strainer
- K-8813 Manual Sink Strainer with Tailpiece
- K-8814 Sink Strainer

**Components**

- Product includes:  
91915 Hardware Kit




ADA

**Codes/Standards**

- ASME A112.19.3/CSA B45.4
- ADA
- ICC/ANSI A117.1

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

|                     |  |
|---------------------|--|
| Bowl configuration: | Single   |
| Installation:       | Under-mount  |
| Bowl area (Only):   | Length: 16-1/2" (419 mm)<br>Width: 13-3/4" (349 mm)<br>Bowl depth: 7-5/8" (194 mm) |
| Drain hole:         | 3-5/8" (92 mm)   |
| Template:           | 1016736-7, required, included  |

### Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.